

ProStock

Flexible Carousel Dispensing



CribMaster ProStock

So you want a device that takes up very little space, has the flexibility to handle multiple sized products, is easily reconfigured and provides high-secure, single item dispensing? You have now found it.

Take the ease and security of carousel dispensing and add flexible carousel sizes, simple on-site reconfigurability and high capacity in a very small footprint, and you have the CribMaster ProStock. If you work in a cellular work design, why would you keep the necessary production tooling right next to the machine? Reduce hoarding, stock-outs, overstock situations, and travel time to the tool crib.

ProStock Functions, Features, and Benefits:

- Easy to use touch screen interface
- Tracking with multi-category usage & accounting – Up to seven (six user definable) classifications for tracking and reporting
- Flexible automatic reordering and resupply
- Item issue security – limit access to prevent incorrect usage or unauthorized access
- Item issue efficiency – improved productivity by issuing nearer to job sites with fast item issue speeds
- Manufacturing efficiency help – machine usage is improved by minimizing downtimes because of inventory shortage
- Eliminate stock-outs with features like critical alerts and automated optimum order levels
- Add inventory dispensing to your work cells for a leaner work flow
- Reduce tool usage 20 - 40% or more
- Automate replenishment with direct communication to your distributors

Dimensions: 82" Tall x 34" Wide x 34.75" Deep

Weight: Approx. 625 lbs unstocked



Product	Divisions per carousel	Area In. ²	Height In.	Volume In. ³	Max diagonal In.	Single division internal widths in inches at different depths in the bin		
						From center	Open-ing	Effective depth
Single division	56	5.3	5.2	27.7	11.05			
Double division	28	10.7	5.2	55.5	11.05	11.0	1.13	0.0
Triple division	18	16.0	5.2	83.2	11.05	10.5	1.08	0.5
Quadruple division	14	21.3	5.2	110.9	11.05	10.0	1.02	1.0
5 division	11	26.7	5.2	138.7	11.05	9.5	.97	1.5
6 division	9	32.0	5.2	166.4	11.05	9.0	.91	2.0
7 division	8	37.3	5.2	194.1	11.05	8.5	.85	2.5
8 division	7	42.7	5.2	221.9	11.05	8.0	.80	3.0
1/4 carousel	4	74.7	5.2	388.2	11.05	7.5	.84	3.5

ProStock

Flexible Carousel Dispensing



Cabinet Specifications

Table 1: Electrical

Parameter	Value
Input voltage	115-240V AC
Frequency	50/60 Hz
Max. Current	4.2 A
Protection Class	Class 1 (connected to protective earth ground)

Table 2: Connections


Parameter	Value
Power cord	
- for North America	3 x 16 AWG, rated 13 A @ 125 V, 3m (9ft 10in)
- for Europe	3 x 1mm ² , rated 10 A @ 250 V, 2.5m (8ft 2in)
Network connections	8-positions Ethernet connector (1 x - main cabinet only)
	6-position RS-485 connector (2x)

Table 3: Operating environment

Parameter	Value
Temperature	0°C to 35°C (32°F to 95°F)
Humidity	10% to 90% (no condensation)

Table 4: Storage environment

Parameter	Value
Temperature	-10°C to 45°C (14°F to 113°F)
Humidity	10% to 90% (no condensation)



LOCKHEED SMALL BUSINESS OF THE YEAR

BOEING SUPPLIER OF THE YEAR

TECHNOLOGY PROVIDER TO THE INDUSTRIAL SUPPLY



technology provider

1955 West Oak Circle - Marietta, GA 30062 - www.cribmaster.com
 phone: 888.419.1399 - fax: 770.419.1968 - sales@wwga.com




ProStock

Flexible Carousel Dispensing



CribMaster

Inventory Management System




lockers replace one carousel

Usable Carousel Bin Dimensions (up to 10 space door opening)*

Section Divide	Depth In.	Height In.	Front Width	Back Width
1	9.6	4.75	1.2	0
2	9.6	4.75	2.4	.19
3	9.6	4.75	3.6	.38
4	9.6	4.75	4.8	.56
5	9.6	4.75	6	.75
6	9.6	4.75	7.2	.94
7	9.6	4.75	8.4	1.13
8	9.6	4.75	9.6	1.32
9	9.6	4.75	10.8	1.51
10	9.6	4.75	12	1.70

* can utilize up to 1/4 carousel (14 spaces) but door opens to only 10. If access and removal can take place through the 10 door measurement 1/4 carousel division can be used.



Usable Locker Dimensions (Inside useable space dimensions)

Locker	Depth In.	Height In.	Width
1-door	28"	4"	23.5"
2-door	28"	4"	11"
3-door	28"	4"	7.5"
6-door	28"	4"	3.5"